







- Ergonomic design
- High power transfer
- Long-life product

Technical Info

Packing

Tec Gun for cartridges 18/1	315200000
Tec7 Manual Gun 600ml sausage 18/1	315501290

Product

Characteristics

The Tec Gun is used for squirting most products in the tube, irrespective of the viscosity, and even for two-part products with its 18:1 pump ratio.

The Tec Gun has a pre-tensioning option to enable clean finishing. The Tec Gun has a pressure rod in stainless steel with suspension

The Tec Gun has a strengthened transmission system.

The Tec Gun is ergonomic in use due to its perfect balance and a turning butt to keep the nozzle in the correct position.

Use

- Cut cartridge open and screw on the nozzle.
- · Cut off the nozzle to the required size.
- Place the cartridge in the holder (extractor at the back).
- · The red lip on the de-tensioner has two options: downwards for a continuous pressure, recommended when working with hard products such as X-Tack, and upwards for slight withdrawal to limit the running of softer products such as X-Seal.







